



**Double deck headers right angle  
solder pin, 1 x 1 mm / 0.039 x 0.039 in  
pin spacing 3.81 mm / 0.15 in 100%  
protected against mismatching without  
support mating  
734-432 TO 734-442**

<b>ITEM-NO. (ITEM-NO.)</b>	734-436
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.81
<b>P (NO. OF POLES)</b>	6
<b>Height (Height / mm)</b>	23
<b>Width (Width / mm)</b>	24.95
<b>Depth (Depth / mm)</b>	16.8
<b>COLOR (COLOR)</b>	orange
<b>Comment (Comment)</b>	L1 = No. Of poles / 2 - 1) x Pin Spacing + 5.9 mm
<b>Dimensions (Dimensions)</b>	1.4 + 0.1 mm