



**Female plug with straight solder pin  
pin spacing 3.81 mm / 0.15 in 100%  
protected against mismatching with  
codig fingers**  
734-502 TO 734-520

<b>ITEM-NO. (ITEM-NO.)</b>	734-506
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.81
<b>P (NO. OF POLES)</b>	6
<b>Height (Height / mm)</b>	14.65
<b>Width (Width / mm)</b>	24.36
<b>Depth (Depth / mm)</b>	10.5
<b>No. of connection Points (No. of connection Points)</b>	6
<b>No. of potentials (No. of potentials)</b>	6
<b>COLOR (COLOR)</b>	orange
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 1,5 mm
<b>Dimensions (Dimensions)</b>	1,4 +0,1 mm