



**Female plug with right angled solder
pin pin spacing 3.5 mm / 0.138 in 100%
protected against mismating with
codig fingers**
734-532 TO 734-554

ITEM-NO. (ITEM-NO.)	734-548
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	18
Height (Height / mm)	10.5
Width (Width / mm)	64.5
Depth (Depth / mm)	14.65
No. of connection Points (No. of connection Points)	18
No. of potentials (No. of potentials)	18
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1,4 +0,1 mm