



**Female plug with right angled solder  
pin pin spacing 3.5 mm / 0.138 in 100%  
protected against mismating with  
codig fingers**  
734-532 TO 734-554

|   |  |
|---|--|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 734-554  |
| <b>Measured voltage (Measured voltage / V)</b>              | 160  |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 2.5  |
| <b>Pollution degree (Pollution degree)</b>                  | 2  |
| <b>Current intensity (Current intensity / A)</b>            | 10   |
| <b>RM (PIN SPACING / mm)</b>                                | 3.5  |
| <b>P (NO. OF POLES)</b>                                     | 24   |
| <b>Height (Height / mm)</b>                                 | 10.5   |
| <b>Width (Width / mm)</b>                                   | 85.5   |
| <b>Depth (Depth / mm)</b>                                   | 14.65  |
| <b>No. of connection Points (No. of connection Points)</b>  | 24   |
| <b>No. of potentials (No. of potentials)</b>                | 24   |
| <b>COLOR (COLOR)</b>  | lichtgrau  |
| <b>Comment (Comment)</b>                                    | $L = (\text{No. of poles} \times \text{Pin Spacing}) + 1,5 \text{ mm}$ |
| <b>Dimensions (Dimensions)</b>                              | 1,4 +0,1 mm  |