



**Female plug with right angled solder
pin pin spacing 3.81 mm / 0.15 in 100%
protected against mismatching with
codig fingers**
734-562 TO 734-580

ITEM-NO. (ITEM-NO.)	734-574
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	14
Height (Height / mm)	10.5
Width (Width / mm)	54.84
Depth (Depth / mm)	14.65
No. of connection Points (No. of connection Points)	14
No. of potentials (No. of potentials)	14
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1,4 +0,1 mm