



**Female plug with right angled solder
pin pin spacing 3.81 mm / 0.15 in 100%
protected against mismating with
codig fingers**
734-562 TO 734-580

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 734-576 |
| Measured voltage (Measured voltage / V) | 160 |
| Measured shock voltage (Measured shock voltage / kV) | 2.5 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 10 |
| RM (PIN SPACING / mm) | 3.81 |
| P (NO. OF POLES) | 16 |
| Height (Height / mm) | 10.5 |
| Width (Width / mm) | 62.46 |
| Depth (Depth / mm) | 14.65 |
| No. of connection Points (No. of connection Points) | 16 |
| No. of potentials (No. of potentials) | 16 |
| COLOR (COLOR) | orange |
| Comment (Comment) | L = (No. of poles x Pin Spacing) + 1,5 mm |
| Dimensions (Dimensions) | 1,4 +0,1 mm |