

---

PRODUCT-DETAILS

# HSB250-C

## SHRINK KON BOX - 7,5M TRANSP.



---

### General Information

Extended Product Type	HSB250-C
Product ID	7TCA017300R0342
EAN	5414363104261
Catalog Description	SHRINK KON BOX - 7,5M TRANSP.
Long Description	Thin Wall Heat Shrink Tubing in Dispenser Box - 1/4 Inch Expanded Inside Diameter - 7.5 Meters Transparent

---

### Ordering

EAN	5414363104261
UPC	786210627410
Country of Origin	Germany (DE)
Selling Unit of Measure	each

---

### Dimensions

Product Net Depth / Length	24.6 in 7.5 m
----------------------------	------------------

---

### Container Information

---

Package Level 1 Units	1 piece
Package Level 1 Width	2.4 in 61 mm
Package Level 1 Height	6.7 in 170 mm
Package Level 1 Depth / Length	6.7 in 170 mm
Package Level 2 Units	60 piece
Package Level 2 Width	15.8 in 401 mm
Package Level 2 Height	22.5 in 572 mm
Package Level 2 Depth / Length	20.9 in 531 mm

### Additional Information

Brand / Label	Shrink-Kon
Color	Transparent
Dielectric Test Voltage	280/Mil (11kV/mm) V
Effective Date	19980621
Flammability Hazard Rating	Self Extinguishing
Process Temperature Rating	-67 to +212 °F -55 to +100 °C
Product Name	Plastic conduit
Product Type	Thin-Wall Heat Shrinkable Tubing
RoHS Date	9AKK107992A8965
Shrink Ratio	2:1
Shrink Temperature	230 °F 110 °C
Thickness	Thin
Water Absorption	0.03%

### Certificates and Declarations

Data Sheet, Technical Information	HSB250-C
-----------------------------------	----------

### Classifications

ETIM 6	EC000217 - Shrink tubing
ETIM 7	EC000217 - Shrink tubing
ETIM 8	EC000217 - Shrink tubing
UNSPSC	39121723
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5073 >> Heat shrinkable tube

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Identification & Heat Shrink

