

DATASHEET

PVC Standard Insulating Tape

Version
10/15



Conrad Best-Nr.	Color	Width	Length / Roll
541124	Black	19mm	10 meter
540915	White	19mm	10 meter
541611	Blue	19mm	10 meter
541671	Red	19mm	10 meter
541557	Green	19mm	10 meter
548087	Yellow	19mm	10 meter
548103	Grey	19mm	10 meter
548122	Brown	19mm	10 meter
548141	Orange	19mm	10 meter
548160	Violet	19mm	10 meter
541284	Green / Yellow	19mm	10 meter
545505	Black	19mm	25 meter
545490	White	19mm	25 meter
546665	Blue	19mm	25 meter
545478	Red	19mm	25 meter
545435	Green	19mm	25 meter
548227	Yellow	19mm	25 meter
548213	Grey	19mm	25 meter
548242	Brown	19mm	25 meter
548198	Orange	19mm	25 meter
548182	Violet	19mm	25 meter
545423	Green / Yellow	19mm	25 meter

Dimension tolerance: W: +/-1mm / L: +/-10%

Backing structure.....	Polyvinyl Chloride(PVC)
Base Adhesion	Rubber
Total Thickness	0.13mm
180° peel Adhesion	≥ 1N / cm
Tensile Strength	15N / cm
Ultimate Elongation	160%
Voltage Rating	600V
Breakdown Voltage	1.5kV
Operating Temperature	-10 ~ 80°C
Storage Temperature	-10 ~ 80°C
Operating Humidity	90%RH
Storage Humidity	90%RH
Other information	Resistance to abrasion , moisture, Chemicals....etc



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2015 by Conrad Electronic SE.