



Cable Ties without serration in flexible TPU

- SOFTFIX-Family
- SRT-Series for industry quantities

Features and Benefits

Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: UV and weather resistant, strong yet elastic, and suitable for temperatures as low as -40 degrees C. The SRT ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres, cable harnesses.

Application

The SRT range offers solutions to numerous bundling applications. The soft, flexible material makes these ties particularly suitable for use on data and fibre-optic cables. The elasticity of the material makes them ideal for securing young trees to support poles, and other applications within the gardening and landscaping industry.



The Elasticity of the SOFTFIX ties makes them suitable for use in many applications.



SOFTFIX ties available in small quantities.




New:

with 2nd loop to run bundles in parallel!

Material Data

Material	Thermoplastic Polyurethane (TPU)
Colour	Black (BK)
Operating Temperature	-40 °C to +85 °C
Flammability	UL94 HB



SRT Series

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Pack Cont.
SOFTFIX-Family							
115-07190	SOFTFIX XS	180	7.0	45.0	57	TPU	16
115-07270	SOFTFIX S	260	7.0	79.0	57	TPU	12
115-11270	SOFTFIX M	260	11.0	55.0	123	TPU	8
115-11350	SOFTFIX L	340	11.0	90.0	123	TPU	6
115-28590	SOFTFIX XL	580	28.0	150	360	TPU	3
SRT-Series							
115-07189	SRT1807	180	7.0	45.0	57	TPU	16
115-07269	SRT2607	260	7.0	79.0	57	TPU	50
115-11269	SRT26011	260	11.0	55.0	123	TPU	50
115-11349	SRT34011	340	11.0	90.0	123	TPU	50
115-28589	SRT58028	580	28.0	150	360	TPU	10
115-28889	SRT88028	880	28.0	240	360	TPU	180

All dimensions in mm. Subject to technical changes.