



Carrier Marking System, laser

• Helafix HC Carriers

Features and Benefits

The versatile Helafix HC and HCR character carriers are suitable for temporary or permanent marking. They are fixed in place using series T18 cable ties, screws or rivets. They are also easy to attach for temporary marking. Material and profile reliably protect the inserted label against damp, dirt, damage and UV radiation.

Helafix HC is supplied as cut lengths in bags, pre-cut and pre-punched. Helafix HCR is supplied in reel format and can be cut to size with the appropriate HCT tools.

We recommend HFX labels printed on an office laser printer using our Tagprint Pro labelling software.

Application

Marking of cable looms, cables, pipes, transport systems, valves, sensors, for inventory marking on machines or other parts.



Multi-purpose identification potential: Helafix HC and HCR.

Material Data

Material	Polyethylene, UV Resistant (PEUV)
Colour	Transparent (CL)
Operating Temperature	-60 °C to +65 °C
Flammability	UL94 HB
Chem. Material Properties	Excellent resistance to UV light, oils, water and a variety of solvents.



Technical Table

Article-No.	Type	Length (L)	Height (H)	Recommended Labels	Pack Cont.	Reel Length	Application Tool
Helafix HC							
525-07173	HC06-17	17.5	7.00	-	50	-	-
525-07353	HC06-35	35.0	7.00	-	50	-	-
525-10173	HC09-17	17.5	10.00	HFX9-17P	50	-	-
525-10353	HC09-35	35.0	10.00	HFX9-35P	50	-	-
525-10523	HC09-52	52.0	10.00	HFX9-52P	50	-	-
525-13173	HC12-17	17.5	13.00	-	50	-	-
525-13353	HC12-35	35.0	13.00	HFX12-35P	50	-	-
525-13523	HC12-52	52.0	13.00	HFX12-52P	50	-	-
525-13703	HC12-70	70.0	13.00	-	50	-	-
525-19353	HC 18-35	35.0	19.00	-	50	-	-
525-19523	HC 18-52	52.0	19.00	-	50	-	-
525-19703	HC 18-70	70.0	19.00	-	50	-	-
525-25523	HC 24-52	52.0	25.00	-	50	-	-
525-25703	HC 24-70	70.0	25.00	-	50	-	-
Helafix HCR							
525-07003	HCR 06	-	7.00	-	25	25.0 m	-
525-10003	HCR 09	-	10.00	HFX9	25	25.0 m	HCT1
525-13003	HCR 12	-	13.00	HFX12	25	25.0 m	HCT2
525-19003	HCR 18	-	19.00	-	-	25.0 m	-
525-25003	HCR 24	-	25.00	-	-	25.0 m	-

All dimensions in mm. Subject to technical changes.

Technical Table

Article-No.	Type	For Carrier Width	For Size	Ø D
Helafix HCT tang				
525-00010	HCT1	10.00	HCR09	2.5
525-00013	HCT2	13.00	HCR12	2.5

All dimensions in mm. Subject to technical changes.

We recommend as suitable labels Helafix HFX, see page 514.

