



Cable Cover, Material: PP

• Helawrap HWPP

Features and Benefits

Helawrap is the ideal solution for bundling and protecting cables in industrial as well as in home or office environments. Due to its special profile and handy applicator tool, Helawrap can be applied rapidly and effortlessly. The unique design allows the user to branch off cable at any point along the cover with ease. Helawrap can also be removed and re-applied as often as required.

Helawrap is available in several colours, a large range of sizes covering most standard applications and in two durable materials. A handy applicator tool is always included.

Application

Helawrap is used to bundle and protect cables in the electrical industry, panel building, machine, automotive and truck manufacturing. Helawrap in 25m lengths is the time-saving solution for industrial applications. Due to its excellent flame-retardant properties, Helawrap Polyamide 6 V0 is the product of choice wherever fire protection is essential, for example in mass transit.

Helawrap in practical 2m lengths is designed for domestic and office use. It puts an end to the cable chaos associated with PCs, TVs and Hi-Fi systems.



Complete cable management for home and office.



Helawrap, the fast and easy solution to your cable chaos, available in 2 sizes and 3 colours!

Material Data	
Material	Polypropylene (PP)
Operating Temperature	-60 °C to +110 °C, Intermittent +140 °C
Flammability	UL94 HB



Technical Table

Article-No.	Type	Colour	Bundle Ø max.	Wall (WT)	Application Tool
HWPP 2m lengths					
161-64204	HWPP16L2	Black (BK)	16	0.80	HAT16
161-64205	HWPP16L2	Grey (GY)	16	0.80	HAT16
161-64206	HWPP16L2	Silver (SR)	16	0.80	HAT16
161-64404	HWPP25L2	Black (BK)	27	1.05	HAT25
161-64405	HWPP25L2	Grey (GY)	27	1.05	HAT25
161-64406	HWPP25L2	Silver (SR)	27	1.05	HAT25
HWPP 25m lengths					
161-64101	HWPP8	Black (BK)	9	0.75	HAT8
161-64102	HWPP8	Grey (GY)	9	0.75	HAT8
161-64103	HWPP8	Silver (SR)	9	0.75	HAT8
161-64104	HWPP8	White (WH)	9	0.75	HAT8
161-64201	HWPP16	Black (BK)	16	0.80	HAT16
161-64202	HWPP16	Grey (GY)	16	0.80	HAT16
161-64203	HWPP16	Silver (SR)	16	0.80	HAT16
161-64207	HWPP16	White (WH)	16	0.80	HAT16
161-64301	HWPP20	Black (BK)	21	0.95	HAT20
161-64302	HWPP20	Grey (GY)	21	0.95	HAT20
161-64303	HWPP20	Silver (SR)	21	0.95	HAT20
161-64304	HWPP20	White (WH)	21	0.95	HAT20
161-64401	HWPP25	Black (BK)	27	1.05	HAT25
161-64402	HWPP25	Grey (GY)	27	1.05	HAT25
161-64403	HWPP25	Silver (SR)	27	1.05	HAT25
161-64407	HWPP25	White (WH)	27	1.05	HAT25
161-64501	HWPP30	Black (BK)	32	1.30	HAT30
161-64502	HWPP30	Grey (GY)	32	1.30	HAT30
161-64503	HWPP30	Silver (SR)	32	1.30	HAT30
161-64504	HWPP30	White (WH)	32	1.30	HAT30

All dimensions in mm. Subject to technical changes.