



Anschließbare Leitung  
Ø 6 ... 8 mm / 0,14 - 0,5 mm<sup>2</sup>



## Technical Data

Connection type	M12 plug
No. of poles	5
Anschlusspunkt geschirmt	yes
Leitungsanschlussrichtung zur Steckrichtung	0°
Steckgesichtskodierung Leitung/Adapter 1 1	B coded

## Connection data

Connection type (1)	Federtechnik
Solid conductor	0.14 ... 0.5 mm <sup>2</sup> / ...

## Mechanical data

Connectable sheathed cable diameter	6 ... 8 mm
Weight	44 g

## Environmental Requirements

Surrounding air (operating) temperature	-40 ... 85 °C
Degree of protection	IP67

## Commercial data

Country of origin	DE
GTIN	4045454639891
Customs Tariff No.	85369010000

## Downloads

### Documentation

#### System Description

767 Series, SPEEDWAY accessories, data sheet	May 16, 2018	1.0 MB	<a href="#">Download</a>
--	--------------	--------	--------------------------

Subject to changes.