



Anschließbare Leitung  
Ø 6,5 ... 10,5 mm / max. 2,5 mm<sup>2</sup>

#### Data

##### Technical Data

Connection type	M23 socket
No. of poles	6
Leistungsanschlussrichtung zur Steckrichtung	90°

##### Connection data

Connection type (1)	Löttechnik
---------------------	------------



Solid conductor	2.5 mm <sup>2</sup>
-----------------	---------------------

---

### Mechanical data

Connectable sheathed cable diameter	6.5 ... 10.5 mm
Weight	139.66 g

---

### Environmental Requirements

Degree of protection	IP67
----------------------	------

---

### Commercial data

Packaging type	bag
Country of origin	DE
GTIN	4045454434816
Customs Tariff No.	85366990990
Product Group	23 (I/O passive and accessories)

---

### Downloads

#### Documentation

#### System Description

767 Series, SPEEDWAY accessories, data sheet	May 16, 2018	1.0 MB	<a href="#">Download</a>
--	--------------	--------	--------------------------

---

Subject to changes.