



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MATERIAL: LOW DENSITY POLYETHYLENE

PART NO.	DIMENSIONS		WEIGHT lbs / 100 ft (g) / 100 ft
	A	B	
CLT25F -	0.397 (10.10)	0.277 (7.03)	0.75 (340.0)
CLT35F -	0.500 (12.7)	0.350 (8.89)	1.12 (510.0)
CLT38F -	0.556 (14.12)	0.415 (10.54)	1.38 (625.0)
CLT50F -	0.670 (17.02)	0.505 (12.83)	1.85 (840.0)
CLT62F -	0.816 (20.72)	0.650 (16.50)	2.29 (1040.0)
CLT75F -	0.935 (23.75)	0.760 (19.30)	2.64 (1200.0)
CLT100F -	1.090 (27.69)	0.915 (23.24)	3.52 (1600.0)
CLT125F -	1.500 (38.10)	1.290 (32.77)	6.03 (2740.0)
CLT150F -	1.728 (43.89)	1.480 (37.59)	7.39 (3360.0)
CLT188F -	2.169 (55.1)	1.881 (47.8)	9.10 (4127.3)

TUBING IS TO BE SLIT
IN ONE PLACE DOWN ITS
ENTIRE LENGTH



NOTES:

- SEE PART NUMBER SUFFIX DESIGNATION ON CURRENT PRICE SHEET FOR PACKAGE SIZE.
- COLOR:
 - 3 DENOTES ORANGE
 - 4 DEONTES YELLOW

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

CAD FILENAME/LAYERS

G00222BF_PB_CLTF_06



CORP. TINLEY PARK, ILLINOIS

CLT()F -
SLIT CORRUGATED TUBING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± 0.050
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CMR

MAT'L:

SCALE NONE

DATE 7-10-95

SEE ABOVE

DRAWING NO.

G00222BF

DWG

A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
6	9/25/02	LGG		CHG MATERIAL TO LOW DENSITY POLYETHYLENE	GB0222BF	6		
5	4/15/02	LGG		CHG DIM 'A' & 'B' ON CLT150F WAS 1.850 (47.00) & 1.550 (39.37)	GB0222BF	5		
4	8/15/00	JAD		ADDED CLT188F - CHANGED ADDING FOR -4 (YELLOW) PRODUCTS CHANGED CAD FILE NAME, CHANGED NOTE 2	GB0222BF	4		