



**Female connector with snap-in
mounting foot and direct contact of
the earth conductor 4 pole with
moulded pole marking switchable
267-124**

| | |
|-------------------------------------------------------------|---------|
| ITEM-NO. (ITEM-NO.) | 267-124 |
| Cross section1 (Cross section / mm²) | 0.5 - 1 |
| Cross section2 (Cross section / AWG) | 22 - 18 |
| Strip length (Strip length / mm) | 8 - 8 |
| Measured voltage (Measured voltage / V) | 500 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 6 |
| P (NO. OF POLES) | 4 |
| Height (Height / mm) | 34 |
| Width (Width / mm) | 32 |
| Depth (Depth / mm) | 32 |
| COLOR (COLOR) | weiß |
| WEIGHT (WEIGHT / g) | 7.85 |