



**Female connector with snap-in  
mounting foot and direct contact of  
the earth conductor 5 pole with  
moulded pole marking switchable  
267-175**

<b>ITEM-NO. (ITEM-NO.)</b>	267-175
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.5 - 1
<b>Cross section2 (Cross section / AWG)</b>	22 - 18
<b>Strip length (Strip length / mm)</b>	8 - 8
<b>Measured voltage (Measured voltage / V)</b>	500
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	6
<b>P (NO. OF POLES)</b>	5
<b>Height (Height / mm)</b>	34
<b>Width (Width / mm)</b>	26
<b>Depth (Depth / mm)</b>	42
<b>COLOR (COLOR)</b>	weiß
<b>WEIGHT (WEIGHT / g)</b>	10.022