



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MATERIAL: NYLON 6

MATERIAL: LOW DENSITY POLYETHYLENE

PART NO.	DIMENSIONS		WALL THICKNESS	WEIGHT lbs / 100 ft (g)
	A	B		
CLT25N-630	0.397 (10.08)	0.277 (7.04)		0.81 (370.0)
CLT35N-630	0.500 (12.7)	0.350 (8.89)		1.28 (580.0)
CLT38N-630	0.556 (14.12)	0.415 (10.39)		1.47 (670.0)
CLT50N-630	0.670 (17.02)	0.505 (12.83)		1.98 (900.0)
CLT62N-630	0.816 (20.73)	0.650 (16.51)		2.39 (1085.0)
CLT75N-630	0.935 (23.75)	0.760 (19.30)		2.75 (1250.0)
CLT100N-630	1.090 (27.69)	0.915 (23.24)		3.70 (1680.0)
CLT125N-630	1.500 (38.10)	1.290 (32.77)		5.77 (2620.0)
CLT150N-630	1.728 ±0.085 (43.89 ±2.16)	1.479 ±0.085 (37.57 ±2.16)		6.16 (2800.0)
CLT188N-630	2.169 ±0.085 (55.09 ±2.16)	1.881 ±0.085 (47.78 ±2.16)		11.20 (5088.00)

PART NO.	DIMENSIONS		WALL THICKNESS	WEIGHT lbs / 100 ft (g)
	A	B		
CLT25F-20	0.397 (10.08)	0.277 (7.04)	.0155" ± .0025"	0.75 (340.0)
CLT35F-20	0.500 (12.7)	0.350 (8.89)	.0200" ± .0050"	1.12 (510.0)
CLT38F-20	0.556 (14.12)	0.415 (10.39)	.0200" ± .0050"	1.38 (625.0)
CLT50F-20	0.670 (17.02)	0.505 (12.83)	.0200" ± .0050"	1.85 (840.0)
CLT62F-20	0.816 (20.73)	0.650 (16.51)	.0200" ± .0050"	2.29 (1040.0)
CLT75F-20	0.935 (23.75)	0.760 (19.30)	.0200" ± .0050"	2.64 (1200.0)
CLT100F-20	1.090 (27.69)	0.915 (23.24)	.0200" ± .0030"	3.52 (1600.0)
CLT125F-20	1.500 (38.10)	1.290 (32.77)	.0235" ± .0065"	6.03 (2740.0)
CLT150F-20	1.729 ±0.085 (43.92 ±2.16)	1.482 ±0.085 (39.64 ±2.16)	.0235" ± .0065"	7.39 (3360.0)
CLT188F-20	2.169 ±0.085 (55.09 ±2.16)	1.881 ±0.085 (47.78 ±2.16)	.0235" ± .0065"	9.10 (4127.3)



NOTES:

- SEE PART NUMBER SUFFIX DESIGNATION ON CURRENT PRICE SHEET FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

CAD FILENAME/LAYERS: G00222BP_DC_06

PANDUIT CORP. TINLEY PARK, ILLINOIS

CLT()N, CLT()F
SLIT CORRUGATED TUBING

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
6	9/25/02	LGG		CHG MAT. TO LOW DENSITY POLYETHYLENE	GB0222BP	6		
5	4/5/02	LGG		CHG DIM ON A & B DIM FOR CLT150N, CLT150F.	GB0222BP	5		
				A WAS 1.785 (45.34) *B* WAS 1.550 (39.37) ON BOTH				
4	4-23-01	LGG		ADDED WALL THICKNESS	GB0222BP	4		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (XXX) ± 0.050 (1.27)
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

SCALE: NONE

DRAWING NO. GB0222BP

DWG SIZE: A

DRAWN BY: CPE MAT'L: SEE ABOVE

DATE: 9-18-97

CHK'D: