

Insert strip - ESL 24X 4 - 0808231

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Figure shows the ESL 29 x 8 version

Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office printing systems, Plotter, Perforated and ruled, Mounting type: Insert, Lettering field: 24 x 4 mm

Product Features

- ☒ Insert labels for plastic cable markers

Key commercial data

package_quantity	10
GTIN	4017918171520

Technical data

Dimensions

Length (b)	24 mm
Width (a)	4 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	Print image may vary depending on laser printer
Color	white
Components	free from silicone and halogen
Material	Polyester foil
Number of individual labels	488
Number of individual labels per row	8

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137

Insert strip - ESL 24X 4 - 0808231

classifications

eCl@ss

eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>