

Conductor marker carrier - PATO 2/15 - 1013122

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Conductor marker carrier, transparent, Unlabeled, Mounting type: Clip on, Cable diameter: 2.8-4.4 mm, Lettering field: 4 x 15 mm

The figure shows a similar product

Product Features

- ✓ Can be labeled using UC-WMT ... and US-WMT ... plastic labels or EMT insert strips
- ✓ These marking collars are used for subsequent labeling of systems that have already been wired

Key commercial data

package_quantity	1000
GTIN	4017918013547

Technical data

Dimensions

Width (a)	15 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

Conductor marker carrier - PATO 2/15 - 1013122

classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>