

Shrink sleeve - WMS 3,2 (30X5)RL - 0800387

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, Perforated, Mounting type: Slide on, Cable diameter: 1-3.2 mm, Lettering field: 30 x 5 mm

The illustration shows WMS 6,4 (30X10)R

Key commercial data

package_quantity	1
GTIN	4046356626545

Technical data

Dimensions

Length (b)	30 mm
Width (a)	5 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-55 °C ... 135 °C

General

Color	white
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Number of individual labels	2000
Number of individual labels per row	2

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

Shrink sleeve - WMS 3,2 (30X5)RL - 0800387

classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

THERMOMARK-RIBBON 64-WMSU - 0801360



THERMOMARK-RIBBON 110-WMSU - 0801358



Printing system accessories

THERMOMARK-ERH 500 - 5146309



Drawings