


Rating	12V DC 8A
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1000V 1minute
Operation Temperature	-0°C~65°C
Fuse	Ø6.4X30



Tolerances ± 0.3 Unless Otherwise Specified

									△
									△
Date	Name	Description						No.	
Drawn	Checked	Approved	SCI BOM No.		Model Name	LIGHTER PLUG			
邱 權		<i>Smart</i>	Customer No.		Model No.	A13-26A		Rev.	
12/13/12		12/14-12	Unit	mm				X0	