

Shrink sleeve - WMS 12,7 (EX20)R - 0800294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X, Unperforated, Mounting type: Slide on, Cable diameter: 4.2-12.7 mm, Lettering field: 20 x 20000 mm

Product Features

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- UL 224 (125°C, 600 V, VW-1)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- CSA.C22.2 No. 198.1 (125°C, 600 V, VW-1)
- Individual markers can be cut to any length up to 1 m

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 1 |
| GTIN | 4046356625845 |

Technical data

Dimensions

| | |
|-------------------|-------|
| Length (b) | 20 m |
| Width (a) | 20 mm |

Ambient conditions

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -55 °C ... 135 °C |

General

| | |
|--|--------------|
| Color | white |
| Base element material | polyolefine |
| Components | Halogen-free |
| Material | Polyolefine |
| Number of individual labels | 660 |
| Number of individual labels per row | 1 |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 24190219 |
|-------------------|----------|

Shrink sleeve - WMS 12,7 (EX20)R - 0800294

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27400401 |
| eCl@ss 5.1 | 27400401 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC001530 |
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

accessories

Ink ribbon

THERMOMARK-RIBBON 64-WMSU - 0801360



THERMOMARK-RIBBON 110-WMSU - 0801358



Printing system accessories

Shrink sleeve - WMS 12,7 (EX20)R - 0800294

accessories

THERMOMARK ROLL-ERH - 5146448



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>