

Conductor marker - UC-WMCO 3,6 (21X4,5) - 0827190

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Conductor marker, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Slide on, Cable diameter: 2.9-3.6 mm, Lettering field: 21 x 4.5 mm

Product Features

- ✓ The UC-WMCO ... UniCard labeling range includes thread-on markers for the subsequent labeling of conductors by simply sliding them on using the UC-WMCO ... TOOL
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements

Key commercial data

package_quantity	10
GTIN	4046356445474

Technical data

Dimensions

Width (a)	21 mm
------------------	-------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	32
Number of individual labels per row	8

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401

Conductor marker - UC-WMCO 3,6 (21X4,5) - 0827190

classifications

eCl@ss

eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Assembly tool

UC-WMCO 3,6 TOOL - 0827804



UC-WMCO TOOL SET - 0827807



Magazine

P1 UC-MAG 7 - 5146568



Conductor marker - UC-WMCO 3,6 (21X4,5) - 0827190

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>