

Cable marker - WMT 2,4 (15X4)R - 0816281

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Thread on, Cable diameter: 1-2.4 mm, Lettering field: 15 x 4.2 mm

Product Features

- ✓ High-quality labeling image created by thermal transfer printing
- ✓ Available for different conductor diameters
- ✓ The special hole geometry ensures a strong axial hold
- ✓ Labeling service: Phoenix Contact can custom-label all conductor markers according to your requirements
- ✓ Custom labeling and easy handling
- ✓ Made from high-quality polyester foil
- ✓ Special packaging protects the conductor markers against external influences, dust, and dirt
- ✓ The conductor to be marked is threaded through two punched holes in the marker and positioned

Key commercial data

package_quantity	1
GTIN	4046356125680

Technical data

Dimensions

Length (b)	29.3 mm
Width (a)	4.2 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Color	white
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	4000
Number of individual labels per row	3

classifications

eCl@ss

Cable marker - WMT 2,4 (15X4)R - 0816281

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>