


Fast-Acting Ferrule Fuses


13/32" x 1-3/8"



Dimensional Data



Time-Current Characteristic Curves—Average Melt



Catalog Symbol: BBS

Fast-Acting
1/10 TO 30A

Interrupting Rating: 10 KA

UL Listed, STD. 248-14

0-5A/600Vac OR LESS, 6-10A/250Vac
(GUIDE #JDYX, FILE #E19180)


CSA CERTIFIED, C22.2 NO. 248.14

0-5A/600V, 6-10A/250Vac
(CLASS #1422-01, FILE #53787)

Electrical Ratings (Catalog Symbol and Amperes)

600Vac		250Vac	48Vac
BBS-1/10	BBS-1	BBS-6	BBS-12
BBS-2/10	BBS-1-1/2	BBS-7	BBS-15
BBS-1/4	BBS-1-6/10	BBS-8	BBS-20
BBS-4/10	BBS-1-8/10	BBS-10	BBS-25
BBS-1/2	BBS-2	—	BBS-30
BBS-6/10	BBS-3	—	—
BBS-3/4	BBS-4	—	—
BBS-8/10	BBS-5	—	—

CE logo denotes compliance with European Union Low Voltage Directive (50-1000Vac, 75-1500Vdc). Refer to Data Sheet: 8002 or contact Bussmann Application Engineering at 636-527-1270 for more information.



Recommended fuseblocks/fuseholders for 13/32" x 1-1/2" fuses

See Data Sheets listed below

- Open fuseblocks - 1104, 2104
- Finger-safe fuseholders - 1109, 1102, 1103, 1151
- Panel-mount fuseholders - 2114, 2113, 2108, 2112, 2109, 2140
- In-line fuseholders - 2127, 2126

- For control circuits, gaseous vapor fixture, HID ballasts; electronic circuits and hand-held meters.
- Fibre Tube.
- Nickel Plated Brass Endcaps.

The only controlled copy of this Data Sheet is the electronic read-only version located on the Bussmann Network Drive. All other copies of this Data Sheet are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.