

Technical Data

Operating voltage	220 - 240 V/AC, 50 Hz
Max. power consumption.....	23 W
Protection class.....	I
Protection type	IP44
Motor speed	2200 rpm
Conveyor capability	180 m ³ /h
Max. noise emission.....	30 dB(A) (at a distance of 3 m)
Temperature of moved air	Max. +45 °C
Ambient temperature	0 °C to max. +45 °C
Required duct diameter	125 mm
Dimensions.....	125 x 110 mm (Ø x L)
Weight.....	550 g