





GE-DP 3925 ECO

Dirt Water Pump

Item No.: 4170710

Ident No.: 11025

Bar Code: 4006825572339

The GE-DP 3925 ECO dirty water pump is a high-quality, extremely efficient and intelligent helper from the ECO Power series. On a wide range of pump tasks everywhere in the home, garden, ponds and wells it convinces by its state-of-the-art features, solid power and optimum energy efficiency with a rating of just 390 W, this pump achieves a delivery rate of up to 10,000 liters of dirty water per hour.

Features

- Ergonomic carrying handle
- Float switch infinitely adjustable in height
- "High-quality mech. seal (ceramic/rubber) for a long service life
- Pump housing made of impact-resistant plastic
- Easily reachable hose connection on the pump's topside
- Integrated suspension eyelet
- Cable rewind
- Universal connector approx. 47.8 mm male thread (G 1 ½)
- ECO Power: higher delivery rate, lower power consumption

Technical Data

- Power 390 W - Max. delivery capacity 10000 L/h - Max. delivery height 6 m - Max. immersion depth 7 m 35 °C - Max. water temperature - Max. size of foreign particles 25 mm

- Hose connection 47,8mm (G11/2 AG) 230 V | 50 Hz - Mains supply - Power cord 10 m | H05RN-F

Logistic Data

- Product weight 5.3 kg - Gross weight single packaging 6.3 kg



















