



Einhell

EXPERT

Dirt Water Pump

GE-DP 6935 ECO

Item No.: 4170720

Ident No.: 11039

Bar Code: 4006825572346

The GE-DP 6935 ECO dirty water pump is a high-quality, powerful and intelligent helper from the ECO Power series. On a wide range of pump tasks everywhere in the home, garden, ponds and wells it convinces by its state-of-the-art features, solid power and optimum energy efficiency – with a rating of just 690 W, this pump achieves a delivery rate of up to 17,500 liters of dirty water per hour.

Features & Benefits

- Ergonomic carrying handle
- Float switch infinitely adjustable in height
- "High-quality mech. seal (ceramic/rubber) for a long service life
- Pump housing made of impact-resistant plastic
- Easily reachable hose connection on the pump's top side
- Integrated suspension eyelet
- Cable rewind
- Universal adapter for 25/32 mm hoses as well as 33.3 mm (G 1)
- ECO Power: higher delivery rate, lower power consumption



Technical Data

- Mains supply 230 V | 50 Hz
- Power 690 W
- Max. delivery capacity 17500 L/h
- Max. delivery height 9 m
- Max. immersion depth 7 m
- Max. water temperature 35 °C
- Max. size of foreign particles 35 mm
- Hose connection 47,8mm (G11/2 AG)
- Power cord 10 m | H07RN-F

Logistic Data

- Product weight 5.497 kg
- Gross weight single packaging 7.697 kg
- Dimensions single packaging 278 x 199 x 423 mm
- Pieces per export carton 4 Pieces
- Gross weight export carton 31.7 kg
- Dimensions export carton 560 x 420 x 440 mm
- Container quantity (20"/40"/40"HC) 1080 | 2240 | 0

