



Einhell

GREY

Electronic flow switch

Art.-No. 41.742.21

Features

- Return valve (1)
- Adapter (2)
- Outlet (3)
- 1.45 m mains cable (4)

Technical Data

- | | |
|----------------------------|---------------------------------|
| ■ Mains: | 220-240 V ~ 50 Hz |
| ■ Max. current: | 10 A |
| ■ Max. operating pressure: | 1 MPa (10 bar) |
| ■ Max. water temperature: | 55°C |
| ■ Screw thread entry: | R 1 (ca. 33.3 mm) male thread |
| ■ Screw thread exit: | R 1 (ca. 33.3 mm) female thread |
| ■ Net Weight: | 1.2 kg |
| ■ Gross Weight: | 1.4 kg |
| ■ Packing dimensions: | 190 x 135 x 165 mm |
| ■ Bar code: | 4006825 549225 |
| ■ Sales unit: | 16 pcs |

