

Manual

Mechanical full day timer

Ref. 15GD/3A, 17GD/3A, 18GD/3A

1. Settings

To define the ON-period of time push the black switching pins at the edge of the turntable until it is engaged (one pin for each 30 min.)

For example: The timer should switch on a lamp during a daily period between 6am and 10am. For that the pins have to be pushed down; each pin corresponds to a time period of 30 min.

For setting of the clock the turntable has to be turned clockwise until the current time corresponds with the marker of the turntable.

Afterwards it is important to plug the timer in the socket outlet immediately, in order to start the mechanical timer.

Side switch:

Position I: manual ON position

Position clock-symbol: programmed ON- and OFF switching.

2. Safety regulations:

Keep this appliance away from children.

To be used only in dry rooms.

The mentioned max. power must not be exceeded.

If necessary the appliance must be repaired only by a certified expert.

3. Specifications

Rated voltage: 230V, 50 Hz

Max. Power: 16A/3680W

Protection degree: IP20

Min. temperature: 0°C

Max. temperature:55°C



Everflourish Electrical Co., Ltd.

Renjiu Village, Wuxiang Town, Yinzhou Ningbo 315111 P.R. China