

## Insertion bridge - EB 2-25/PT - 3260157

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insertion bridge, Number of positions: 2, Color: red

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356779111

### Technical data

#### Technical data

<b>Color</b>	red
<b>Number of positions</b>	2
<b>Maximum load current</b>	150 A
<b>Inflammability class according to UL 94</b>	V0

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27141199
<b>eCl@ss 4.1</b>	27141199
<b>eCl@ss 5.0</b>	27141145
<b>eCl@ss 5.1</b>	27141145
<b>eCl@ss 6.0</b>	27141133
<b>eCl@ss 7.0</b>	27141133
<b>eCl@ss 8.0</b>	27141133

#### ETIM

<b>ETIM 3.0</b>	EC000886
<b>ETIM 4.0</b>	EC000902
<b>ETIM 5.0</b>	EC000902

#### UNSPSC

<b>UNSPSC 6.01</b>	30211827
<b>UNSPSC 7.0901</b>	39121424
<b>UNSPSC 11</b>	39121424
<b>UNSPSC 12.01</b>	39121424

# Insertion bridge - EB 2-25/PT - 3260157

## classifications

### UNSPSC

<b>UNSPSC 13.2</b>	39121424
--------------------	----------

## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>