

Radiator Thermostat Classic Model L



Product features



- Easy to mount without having to drain any water or intervene in the heating system; no special tools required
- Suitable for universal use; compatible with the products of the most popular manufacturers
- Adapts to the radiator dimensions thanks to adaptive control and optional valve limiting; no need for hydraulic adjustment on the radiator
- Automatic frost protection and temperature fall detection
- Valve protection function: Automatic protection against calcification thanks to regular opening and closing of valves
- Individual settings for every day of the week thanks to freely programmable heating and reduction times
- Boost button for heating up the radiator quickly and briefly
- Ready to use straight away thanks to preset programming
- Intuitive operation
- Can be individually tailored to personal routines thanks to 3 freely configurable time programs (7 switching times per day for temperature switchover)
- Precise temperature adjustment (to the nearest 0.5°C)
- Temperature reduced automatically during ventilation (open window detection)
- Tamper-proof thanks to child-proof lock/operating block

Technical specifications

Power supply:	3 V
Max. current consumption:	100 mA
Batteries:	2 x LR6/Mignon/AA
Battery life:	Approx. 3 years (3 heating cycles)
Display:	LCD
Threaded connection:	M30 x 1.5 (e.g. for Heimeier, MNG, Honeywell-Braukmann, Oventrop type A and type AV6, Schlösser, Comap D 805, Valf, Watts, Danfoss RA, RAV and RAVL with adapter)
Dimensions (W x H x D):	58 x 71.5 x 90 mm
Weight:	126.5 g

Logistical data

Product reference:	103740
EAN code:	4047976037407
Short name:	CC-RT-O-CnL-W-R5
Packing unit:	48
Packaging dimensions:	110 x 110 x 75 mm
Total weight:	268.5 g
Customs tariff number:	90321020

Scope of supply

Operating manual in GER, GB, F and NL
2 x mignon batteries/LR6/AA
3 x adapters for Danfoss valves (RA, RAV, RAVL)
Mounting material (1 x screw, 1 x threaded nut)

