

Data Sheet

0.5W LED Daylight 2AA

17651



Designation: 17651

Battery Requirement: 2 x AA

Bulb required: 1pc 0.5W white LED

Luminous intensity: 40 lm or 1150 cd

Range: 67 m (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux).

Weight: 91g (without batteries).

Material: Aluminum
 ABS (Acrylonitrile Butadiene Styrene)
 TPR (Thermoplastic Rubber)
 HIPS (High impact Polystyrene)
 PS (General purpose Polystyrene)

All contact parts made of bronze or nickel plated steel.

| | | |
|-------------------------|----------|-------------|
| Dimensions (mm): | A | 164 |
| | B | 43.5 |
| | C | 31 |
| | D | 41 |

Run Time: 6 hours with VARTA HE

Features (Technical)

- Super bright 0.5W high performance LED
- Push switch (on/off)
- 1 meter impact resistant
- Lanyard
- DC/DC regulator
- Anti-roll feature
- Soft and durable rubber and aluminum grip