

Double-level terminal block - UKK 5-PV - 2791388

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Double-level terminal block, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Connection type: Screw connection, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15, NS 32

Product Description

Levels connected internally

Product Features

- ☒ Large-surface labeling option

Key commercial data

package_quantity	50
GTIN	4017918242787

Technical data

General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	32 A
Nominal voltage U _N	500 V
Open side panel	ja

Dimensions

Width	6.2 mm
Length	56 mm
Height NS 35/7,5	62 mm
Height NS 35/15	69.5 mm

Double-level terminal block - UKK 5-PV - 2791388

Technical data

Dimensions

Height NS 32	67 mm
--------------	-------

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm ²
Cross section with insertion bridge, solid max.	4 mm ²
Cross section with insertion bridge, stranded max.	2.5 mm ²
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120

Double-level terminal block - UKK 5-PV - 2791388

classifications

eCl@ss

eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

UL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	15 A
mm²/AWG/kcmil	26-10

cUL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	15 A
mm²/AWG/kcmil	26-10

GOST 	
---	--

Double-level terminal block - UKK 5-PV - 2791388

approvals



cULus Recognized  US

accessories

Partition plate

DP-UKK 3/5 - 2770794



TS-KK 3 - 2770215



End cover

DG-UKK 3/5 - 2770817



D-UKK 3/5 - 2770024



Double-level terminal block - UKK 5-PV - 2791388

accessories

Warning label printed

WS 5- 6 - 1004403



WS 4- 6 - 1004209



WS 3- 6 - 1004115



Bridge

FB-150 METER - 0201595



FBI 10- 6 - 0203250



Double-level terminal block - UKK 5-PV - 2791388

accessories

FBI 20- 6 - 0201867



FBI 100- 6 - 0201650



EB 2- 6 - 0201155



EB 3- 6 - 0201142



Short-circuit connector

KSS 3- 6 - 0309523



Double-level terminal block - UKK 5-PV - 2791388

accessories

KSS 6 - 0301547



Test plug terminal block

PS-UKK 5 - 3000625



PS-UKK/E - 3000641



RPS - 0201647



Partition plate

ATP-UKK 3/5 - 2778521



Terminal marking

Double-level terminal block - UKK 5-PV - 2791388

accessories

SBS 6:UNBEDRUCKT - 1007222



ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Insulating sleeve

IS-K 4 - 1302338



Double-level terminal block - UKK 5-PV - 2791388

accessories

ISSBI 10- 6 - 0301505



Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Double-level terminal block - UKK 5-PV - 2791388

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Double-level terminal block - UKK 5-PV - 2791388

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Double-level terminal block - UKK 5-PV - 2791388

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Double-level terminal block - UKK 5-PV - 2791388

accessories

Labeled terminal marker

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Double-level terminal block - UKK 5-PV - 2791388

accessories

E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Test socket

PSBJ 3/13/4 - 0201304




PSB 3/10/4 - 0601292



Drawings

Double-level terminal block - UKK 5-PV - 2791388

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>