Feed-through terminal block - UT 4 VT - 3044607

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



The illustration shows various color versions of the article

Feed-through terminal block, Connection method: Screw connection, Cross section: 0.14 mm² - 6 mm², AWG: 26 - 10, Width: 6.2 mm, Color: violet, Mounting type: NS 35/7,5, NS 35/15

Key commercial data

package_quantity	50
GTIN	4017918977252

Technical data

General

Number of levels	1
Number of connections	2
Color	violet
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	41 A (with 6 mm² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I_N	32 A (with 4 mm² conductor cross section)
Nominal voltage U_N	1000 V
Open side panel	ja

Dimensions

Width	6.2 mm
Length	47.7 mm
Height NS 35/7,5	47.5 mm
Height NS 35/15	55 mm

Feed-through terminal block - UT 4 VT - 3044607

Technical data

Connection data

Note	Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area.
Conductor cross section solid min.	0.14 mm²
Conductor cross section solid max.	6 mm²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded min.	0.14 mm²
Conductor cross section stranded max.	6 mm²
Min. AWG conductor cross section, stranded	26
Max. AWG conductor cross section, stranded	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm²
2 conductors with same cross section, solid min.	0.14 mm²
2 conductors with same cross section, solid max.	1.5 mm²
2 conductors with same cross section, stranded min.	0.14 mm²
2 conductors with same cross section, stranded max.	1.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm²
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120

Feed-through terminal block - UT 4 VT - 3044607

classifications

eCl@ss

eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEx / ATEX / CSA / UL Recognized / cUL Recognized / DNV / VDE Gutachten mit Fertigungsüberwachung / cULus Recognized /

Approval details

IECEx	
Nominal voltage UN	690 V
Nominal current IN	30 A
mm²/AWG/kcmil	0.14-4

ATEX

Nominal voltage UN	690 V
Nominal current IN	38 A
mm²/AWG/kcmil	0.14-6

CSA

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A

Feed-through terminal block - UT 4 VT - 3044607

approvals

Usegroups	B	C
mm²/AWG/kcmil	26-10	26-10

UL Recognized

Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm²/AWG/kcmil	26-10	26-10

cUL Recognized

Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm²/AWG/kcmil	26-10	26-10

DNV

VDE Gutachten mit Fertigungsüberwachung

Nominal voltage UN	800 V
Nominal current IN	
mm²/AWG/kcmil	0.2-4

cULus Recognized

accessories

End cover

D-UT 2,5/10 - 3047028



Feed-through terminal block - UT 4 VT - 3044607

accessories

DP PS-6 - 3036738



Partition plate

ATP-UT - 3047167



Screwdriver tools

SZS 0,6X3,5 - 1205053



Marker pen

X-PEN 0,35 - 0811228



Bridge

FBS 2-6 - 3030336



Feed-through terminal block - UT 4 VT - 3044607

accessories

FBS 3-6 - 3030242



FBS 4-6 - 3030255



FBS 5-6 - 3030349



FBS 10-6 - 3030271



FBS 20-6 - 3030365



Feed-through terminal block - UT 4 VT - 3044607

accessories

FBS 50-6 - 3032224



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - UT 4 VT - 3044607

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



Feed-through terminal block - UT 4 VT - 3044607

accessories

NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - UT 4 VT - 3044607

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 6:UNBEDRUCKT - 1051003



Feed-through terminal block - UT 4 VT - 3044607

accessories

UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Labeled terminal marker

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



Test plug terminal block

Feed-through terminal block - UT 4 VT - 3044607

accessories

MPS-MT - 0201744



PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



Feed-through terminal block - UT 4 VT - 3044607

accessories

PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-6 - 3030996



Feed-through terminal block - UT 4 VT - 3044607

accessories

PS-6/2,3MM RD - 3038736



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



Feed-through terminal block - UT 4 VT - 3044607

accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Feed-through terminal block - UT 4 VT - 3044607

accessories

E/NS 35 N - 0800886



Drawings

© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com