

Flange cover - DF-UPBV 2,5/ 4 - 3060432

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Flange cover, Length: 45.7 mm, Width: 4.5 mm, Height: 32 mm, Color: gray

screw version

Product Description

can be snapped onto the UPBV 2,5/... and UPBV 4/... plugs

Product Features

- ✓ For reliable screw connection between the plug and screw flange
- ✓ The flange covers can be snapped onto the plug housing later on

Key commercial data

package_quantity	50
GTIN	4046356147033

Technical data

General

Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C

Dimensions

Width	4.5 mm
Length	45.7 mm
Height	32 mm

Connection data

Tightening torque, min	0.4 Nm
Tightening torque max	0.5 Nm

classifications

eCl@ss

Flange cover - DF-UPBV 2,5/ 4 - 3060432

classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141133
eCl@ss 7.0	27141133
eCl@ss 8.0	27141133

ETIM

ETIM 2.0	EC000886
ETIM 3.0	EC000886
ETIM 4.0	EC000886
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	30211827
UNSPSC 7.0901	39121424
UNSPSC 11	39121424
UNSPSC 12.01	39121424
UNSPSC 13.2	39121424

approvals

GOST /

Approval details

 GOST
--

Drawings