# Printed-circuit board connector - TVFKC 1,5/ 3-ST - 1713842

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



The figure shows a 10-position version of the product

Plug component, Nominal current: 10 A, Rated voltage (III/2): 320 V, Number of positions: 3, Pitch: 5 mm, Connection method: Spring-cage conn., Color: green, Contact surface: Tin

## Product Features

- For 90° actuation in relation to the conductor axis, the TVFKCL 1,5 extended design is required in the lower level of the ME housing
- Front TWIN connection for 1.5 mm²
- Additional actuation option of 90° in relation to the conductor axis

## Key commercial data

| | |
|---|---|
| **package_quantity** | 50 |
| **GTIN** | 4046356093484 |

## Technical data

### Dimensions

| | |
|---|---|
| **Pitch** | 5 mm |
| **Dimension a** | 10 mm |

### General

| | |
|---|---|
| **Range of articles** | TVFKC 1,5/..-ST |
| **Insulating material group** | I |
| **Rated surge voltage (III/3)** | 4 kV |
| **Rated surge voltage (III/2)** | 4 kV |
| **Rated surge voltage (II/2)** | 4 kV |
| **Rated voltage (III/3)** | 250 V |
| **Rated voltage (III/2)** | 320 V |
| **Rated voltage (II/2)** | 630 V |
| **Connection in acc. with standard** | EN-VDE |
| **Nominal current $I_N$** | 10 A |
| **Nominal cross section** | 1.5 mm² |
| **Maximum load current** | 10 A |
| **Insulating material** | PA |
| **Inflammability class according to UL 94** | V0 |
| **Stripping length** | 8 mm |
| **Number of positions** | 3 |

# Printed-circuit board connector - TVFKC 1,5/ 3-ST - 1713842

## Technical data

### Connection data

| | |
|---|---|
| **Conductor cross section solid min.** | 0.2 mm² |
| **Conductor cross section solid max.** | 1.5 mm² |
| **Conductor cross section stranded min.** | 0.2 mm² |
| **Conductor cross section stranded max.** | 1.5 mm² |
| **Conductor cross section stranded, with ferrule without plastic sleeve min.** | 0.25 mm² |
| **Conductor cross section stranded, with ferrule without plastic sleeve max.** | 1.5 mm² Only together with CRIMPFOX ZA3 |
| **Conductor cross section stranded, with ferrule with plastic sleeve min.** | 0.25 mm² |
| **Conductor cross section stranded, with ferrule with plastic sleeve max.** | 1.5 mm² Only together with CRIMPFOX ZA3 |
| **Conductor cross section AWG/kcmil min.** | 24 |
| **Conductor cross section AWG/kcmil max** | 16 |
| **Minimum AWG according to UL/CUL** | 24 |
| **Maximum AWG according to UL/CUL** | 16 |

## classifications

### eCl@ss

| | |
|---|---|
| **eCl@ss 4.0** | 272607xx |
| **eCl@ss 4.1** | 27260701 |
| **eCl@ss 5.0** | 27260701 |
| **eCl@ss 5.1** | 27260701 |
| **eCl@ss 6.0** | 27260704 |
| **eCl@ss 7.0** | 27440402 |
| **eCl@ss 8.0** | 27440402 |

### ETIM

| | |
|---|---|
| **ETIM 3.0** | EC001121 |
| **ETIM 4.0** | EC002638 |
| **ETIM 5.0** | EC002638 |

### UNSPSC

| | |
|---|---|
| **UNSPSC 6.01** | 30211810 |
| **UNSPSC 7.0901** | 39121409 |
| **UNSPSC 11** | 39121409 |
| **UNSPSC 12.01** | 39121409 |
| **UNSPSC 13.2** | 39121409 |

## approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

# Printed-circuit board connector - TVFKC 1,5/ 3-ST - 1713842

## approvals

Approval details

**UL Recognized**

| Usegroups | B | D |
|---|---|---|
| Nominal voltage UN | 300 V | 300 V |
| Nominal current IN | 8 A | 8 A |
| mm²/AWG/kcmil | 24-16 | 24-16 |

**cUL Recognized**

| Usegroups | B | D |
|---|---|---|
| Nominal voltage UN | 300 V | 300 V |
| Nominal current IN | 8 A | 8 A |
| mm²/AWG/kcmil | 24-16 | 24-16 |

**GOST**

**cULus Recognized**

## Drawings

# Printed-circuit board connector - TVFKC 1,5/ 3-ST - 1713842

Diagram




Dimensioned drawing




© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com