

Basic terminal block - UDK-RELG 3 - 2777043

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Basic termination blocks with test connection on both sides and double connections with the same potential for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 3-pos.

The illustration shows versions with a different no. of positions

Key commercial data

package_quantity	10
GTIN	4017918068639

Technical data

Dimensions

Width	20.8 mm
Height	63.6 mm
Depth	113 mm

General

Number of positions	3
Nominal voltage U_N	400 V (voltage is determined by the coupling connector.)
Nominal current I_N	16 A (current is determined by the coupling connector.)
Color	gray
Insulating material	PA

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3

classifications

eCl@ss

Basic terminal block - UDK-RELG 3 - 2777043

classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603

ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001456

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

UL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	15 A
mm²/AWG/kcmil	30-12

cUL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	15 A
mm²/AWG/kcmil	30-12

Basic terminal block - UDK-RELG 3 - 2777043

approvals



cULus Recognized US

accessories

End block

E/UK - 1201442



Bridge

FB-150 METER - 0201595



VS - 3004207



Basic terminal block - UDK-RELG 3 - 2777043

accessories

DB 50- 90 BU - 2821180



DB 50- 90 GY - 2820929



DB 50- 90 BK - 2820916



KB RELG 7 - 2961095



KB RELG 4 - 2961082



KB RELG 3 - 2961079



Basic terminal block - UDK-RELG 3 - 2777043

accessories

KB RELG 2 - 2961066



Mounting material

ZSR - 2303608



Test plug terminal block


RPS - 0201647



Drawings


Basic terminal block - UDK-RELG 3 - 2777043

Dimensioned drawing



Basic terminal block - UDK-RELG 3 - 2777043


Schematic diagram



1-3 = fixed bridge, cross connection rail, spacer

Basic terminal block - UDK-RELG 3 - 2777043

Schematic diagram



1 = Coupling connector 2 = Coding 3 = Cover 4 = Basic termination block

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>