

Cable gland - VC-K-KV-PG21(9-13) - 1853900

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Half screw connection Pg21, made of plastic, consisting of rubber seal with one hole and one pressure screw, for type 2 - 4 housings, cable [mm] 9 - 13

Key commercial data

package_quantity	5
GTIN	4017918145989

Technical data

Dimensions

Wrench size, union nut	33 mm
External cable diameter	9 mm ... 13 mm

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 100 °C

General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Type of the screw connection	Half screw connection
Material, pressure screw	Polyamide
Seal material	TPE
Thread type on seal side	Pg21
Tightening torque, union nut	7.50 Nm

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

Cable gland - VC-K-KV-PG21(9-13) - 1853900

classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441


UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

approvals

GOST /

Approval details



accessories

Half screw connection

VC-K-KV-PG21-O - 1885363

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>