

SCRJ female insert - VS-SCRJ-GOF-BU/BU - 1652978

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



SCRJ socket insert, duplex, for VS-A-F-IP67 panel mounting frame, can be used for fiberglass (multi mode and single mode), HCS, and polymer fibers

Ethernet

Key commercial data

package_quantity	1
GTIN	4017918969943

Technical data

Mechanical characteristics

Number of positions	2
Number of slots	1
Connection profile	SCRJ according to DIN EN 50377-6-1
Fiber type	GOF, HCS, POF
Ferrule diameter	2.50 mm
Number of fibers	2
Insertion/withdrawal cycles	≥ 500
Connection method	female

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Housing material	PBT
Ferrule material	Zirconia ceramics
Ferrule holder color	White

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701

SCRJ female insert - VS-SCRJ-GOF-BU/BU - 1652978

classifications

eCl@ss

eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

GOST /

Approval details



accessories

Adapter

PSM-SET-BFOC-LINK/2 - 2799429



SCRJ female insert - VS-SCRJ-GOF-BU/BU - 1652978

accessories

FL MM PATCH COUPLER LC-LC - 2700312



FL SM PATCH COUPLER LC-LC - 2700313



FL COUPLER SC-DUPLEX - 2901788



PSM-SET-FSMA-LINK/2 - 2799416



Connector set

PSM-SET-SCRJ-DUP/2-POF - 2708656



SCRJ female insert - VS-SCRJ-GOF-BU/BU - 1652978

accessories

PSM-SET-SCRJ-DUP/2-HCS - 2313070



PSM-SET-SCRJ-DUP/2-HCS/PN - 2313546



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>