Accessories - MCC-MT 0,2-0,35 (0,0) BA - 1923717

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Female contact, is inserted into the plug after crimping the conductor, for the module plug housing MCC 1...-STZ-3,81 and MCC 1...--STZF-3,81, for cross sections of 0.2 mm² to 0.34 mm²

Supplied in tape form - please note the drawing.

Key commercial data

package_quantity	8000
GTIN	4017918571450

Technical data

General

Nominal current	4 A
Conductor cross section stranded min.	0.2 mm²
Max. conductor cross section, stranded	0.35 mm²

Connection data

Core diameter including insulation	1.1 mm ... 1.3 mm
Stripping length of individual wires	4 mm

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

Accessories - MCC-MT 0,2-0,35 (0,0) BA - 1923717

classifications

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121410
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

GOST /


Approval details

GOST

Drawings

Accessories - MCC-MT 0,2-0,35 (0,0) BA - 1923717

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com