

Contact insert - HC-M-PN2-6,00-BU - 1676763

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pneumatics female connector, for HC-M-PN2 module, cross section of hose 6.0 mm

Key commercial data

package_quantity	10
GTIN	4017918129415

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
--	-------------------

Mechanical characteristics

Operating pressure, vacuum	8.00 bar
Internal diameter of pressure hose connection	6 mm
Insertion/withdrawal cycles	≥ 500

General

Color	black
--------------	-------

Material data

Contact material	Delrin acetal
-------------------------	---------------

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796

Contact insert - HC-M-PN2-6,00-BU - 1676763

classifications

ETIM

ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

approvals

GOST /

Approval details

 GOST

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>