

## Cover profile - AP 3-TNS 32 - 5022669

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sealable cover profile, for mounting on NS 32 DIN rail, for fixing the cover profile AP 3, with plastic knurled nut M5, space requirement: 13 mm

The figure shows a combination of versions AP 3-TU and AP 3-TNS 32

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4017918095260

### Technical data

#### Dimensions

<b>Height</b>	84 mm
<b>Width (a)</b>	93.5 mm

#### General

<b>Color</b>	gray
<b>Inflammability class according to UL 94</b>	V2
<b>Material</b>	PA

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219
<b>eCl@ss 5.0</b>	27141137
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27141137
<b>eCl@ss 7.0</b>	27144001
<b>eCl@ss 8.0</b>	27144001

#### ETIM

<b>ETIM 2.0</b>	EC001031
<b>ETIM 3.0</b>	EC001031
<b>ETIM 4.0</b>	EC000007
<b>ETIM 5.0</b>	EC000007

# Cover profile - AP 3-TNS 32 - 5022669

classifications

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Drawings

Dimensioned drawing

