

Plastic label - UC-EMLP (60X30) - 0819343

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Adhesive, Lettering field: 60 x 30 mm

Product Features

- ✓ The UC-EMLP ... UniCard labeling range includes self-adhesive device markers with good adhesive properties
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The sheets provide space for including function texts
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

package_quantity	10
GTIN	4046356152426

Technical data

Dimensions

Length (b)	60 mm
Width (a)	30 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	3
Number of individual labels per row	1

classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218

Plastic label - UC-EMLP (60X30) - 0819343

classifications

eCl@ss

eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

P1 UC-MAG 6 - 5146121



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>