

# Cable - CABLE-D-15SUB/F/OE/0,25/S/2,0M - 2926111

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shielded cable with a 15-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 15 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 2 m.

The figure shows the 25-pos. version

## Product Features

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Connector according to IEC 60807-2/DIN 41652
- Open end at one end
- Screw connection: 2 UNC 4-40 screws
- Shield connection: H05V-K 1 mm<sup>2</sup> cable, black, 0.5 m in length
- D-SUB socket or pin strip at one end
- 1:1 connection

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356547970

## Technical data

### General

<b>Nominal voltage U<sub>N</sub></b>	125 V AC/DC
<b>Max. current carrying capacity per path</b>	2 A
<b>Max. conductor resistance</b>	≤ 0.09 Ω/m
<b>Length of cable</b>	2 m
<b>Single wire, cross section</b>	0.25 mm <sup>2</sup>
<b>AWG</b>	24
<b>External diameter</b>	9 mm
<b>Shielding</b>	yes
<b>Shielding</b>	Tinned copper-braided shield, approx. 85% covering
<b>Insertion/withdrawal cycles</b>	> 200

### Environmental conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 50 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C
<b>Flame resistance</b>	IEC 60332-1

# Cable - CABLE-D-15SUB/F/OE/0,25/S/2,0M - 2926111

## Technical data

### Connector, module side

<b>Number of positions</b>	15
<b>Connectors</b>	D-SUB socket strip
<b>Number of plugs</b>	1

### Connector, controller side

<b>Number of positions</b>	15
<b>Connectors</b>	Open end
<b>Number of plugs</b>	0

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 2.0</b>	EC000237
<b>ETIM 3.0</b>	EC000237
<b>ETIM 4.0</b>	EC000237
<b>ETIM 5.0</b>	EC000237

### UNSPSC

<b>UNSPSC 6.01</b>	26121620
<b>UNSPSC 7.0901</b>	26121620
<b>UNSPSC 11</b>	26121620
<b>UNSPSC 12.01</b>	26121620
<b>UNSPSC 13.2</b>	26121620

## approvals

UL Recognized / cUL Recognized / cULus Recognized /


### Approval details



## Cable - CABLE-D-15SUB/F/OE/0,25/S/2,0M - 2926111

approvals

cUL Recognized 

cULus Recognized 

Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>