

## Cover profile - AP-CP-H METER - 3012315

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cover profile, length: 1 m

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356645904

### Technical data

#### General

<b>Color</b>	gray
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PA

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	272607xx
<b>eCl@ss 4.1</b>	27260701
<b>eCl@ss 5.0</b>	27260701
<b>eCl@ss 5.1</b>	27260701
<b>eCl@ss 6.0</b>	27379200
<b>eCl@ss 7.0</b>	27141151
<b>eCl@ss 8.0</b>	27141151

#### ETIM

<b>ETIM 3.0</b>	EC000897
<b>ETIM 4.0</b>	EC000897
<b>ETIM 5.0</b>	EC002848

#### UNSPSC

<b>UNSPSC 6.01</b>	30211802
<b>UNSPSC 7.0901</b>	39121402
<b>UNSPSC 11</b>	39121402
<b>UNSPSC 12.01</b>	39121402
<b>UNSPSC 13.2</b>	39121402

# Cover profile - AP-CP-H METER - 3012315

## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>