

Plastic label - US-EMLP (35X9) - 0828802

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 35 x 9 mm

The figure shows the US-EMLP (20x9) version

Key commercial data

package_quantity	10
GTIN	4046356559041

Technical data

Dimensions

Length (b)	34.65 mm
Height	0.5 mm
Width (a)	9 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-30 °C ... 80 °C

General

Color	white
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Number of individual labels	45
Number of individual labels per row	3

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Plastic label - US-EMLP (35X9) - 0828802

classifications

eCl@ss

eCl@ss 8.0	27141137
------------	----------

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

THERMOMARK CARD-US-MAG1 - 5146451



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>