

Cable lug - C-BCI 2,5/4,6 - 3240569

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Flat pin cable lug, blue, 1.5 - 2.5 mm²,

Product Features

- 'EASY ENTRY' for easy and reliable conductor entry
- Halogen-free
- Electrolytic tin plating

Key commercial data

package_quantity	100
GTIN	4046356563741

Technical data

Dimensions

Length (b)	28.5 mm
Width (a)	4.6 mm
Length contact range	17.5 mm
Length of insulation sleeve (c)	11 mm
Inner dimension of the insulating collar (d)	4.5 mm
Material thickness (g)	0.8 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Short-term temperature	120 °C
Max. permanent temperature	105 °C

General

Color	blue
Stripping length	8 mm
Components	Halogen-free
Inflammability class according to UL 94	V2
Material	Copper

classifications

eCl@ss

Cable lug - C-BCI 2,5/4,6 - 3240569

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400204
eCl@ss 5.1	27400204
eCl@ss 6.0	27400204
eCl@ss 7.0	27400204
eCl@ss 8.0	27400204

ETIM

ETIM 3.0	EC001052
ETIM 4.0	EC001052
ETIM 5.0	EC001052


UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Drawings

Cable lug - C-BCI 2,5/4,6 - 3240569

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>