

Component terminal block - UT 4-MTD-BE - 3046237

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component terminal block, Connection method: Screw connection, Cross section: 0.14 mm² - 6 mm², AWG: 26 - 10, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

The figure shows a version of the article

Key commercial data

package_quantity	50
GTIN	4046356624640

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	0.5 A
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I _N	0.5 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	6.2 mm
Length	57.8 mm
Height NS 35/7,5	40 mm
Height NS 35/15	47.5 mm

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	6 mm ²

Component terminal block - UT 4-MTD-BE - 3046237

Technical data

Connection data

Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	6 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	0.14 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.14 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm ²
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141117
eCl@ss 4.1	27141117
eCl@ss 5.0	27141126
eCl@ss 5.1	27141126
eCl@ss 6.0	27141126
eCl@ss 7.0	27141126
eCl@ss 8.0	27141126

ETIM

ETIM 4.0	EC000902
ETIM 5.0	EC000903

Component terminal block - UT 4-MTD-BE - 3046237

classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST /

Approval details



accessories

End cover

D-UT 2,5/4-TWIN - 3047141



DP PS-6 - 3036738



Screwdriver tools

SZS 0,6X3,5 - 1205053



Component terminal block - UT 4-MTD-BE - 3046237

accessories

Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



Bridge

FBS 2-6 - 3030336



FBS 3-6 - 3030242



FBS 4-6 - 3030255



Component terminal block - UT 4-MTD-BE - 3046237

accessories

FBS 5-6 - 3030349



FBS 10-6 - 3030271



FBS 20-6 - 3030365



FBS 50-6 - 3032224



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Component terminal block - UT 4-MTD-BE - 3046237

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Component terminal block - UT 4-MTD-BE - 3046237

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Component terminal block - UT 4-MTD-BE - 3046237

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Component terminal block - UT 4-MTD-BE - 3046237

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Labeled terminal marker

ZB 6 CUS - 0824992



Component terminal block - UT 4-MTD-BE - 3046237

accessories

UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



Test plug terminal block

MPS-MT - 0201744



PAI-4-N GY - 3032871



PS-6 - 3030996



Component terminal block - UT 4-MTD-BE - 3046237

accessories

PS-6/2,3MM RD - 3038736



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



Component terminal block - UT 4-MTD-BE - 3046237

accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Component terminal block - UT 4-MTD-BE - 3046237

accessories

E/NS 35 N - 0800886



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>