

Zack marker sheet - ZBM 6/WH:UNBEDRUCKT - 5061222

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker sheet, Sheet, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 7.5 x 5.6 mm

Key commercial data

package_quantity	50
GTIN	4017918096281

Technical data

Dimensions

Length (b)	7.5 mm
Width (a)	5.6 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	100
Number of individual labels per row	10
Number of marker strips	10

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Zack marker sheet - ZBM 6/WH:UNBEDRUCKT - 5061222

classifications

eCl@ss

eCl@ss 8.0	27141137
------------	----------

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>